# Technical data sheet

## Cover plate, Telitank T4B, round installation opening for EKR device
## Item number: 7408244

Cover plate with 1 perforation (Ø 45 mm) for one accessory with support ring, suitable for T4B lengthwise side (1/1 cover).

PVC Polyvinylchloride

### Master data

| | |
|---|---|
| Item number | 7408244 |
| Type | T4B P2S 9011 |
| Description 1 | Cover plate |
| Description 2 | 1x EK for T4B |
| Manufacturer | OBO |
| Dimension | 110x77mm |
| Colour | Graphite black; RAL 9011 |
| Material | Polyvinylchloride |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 1.66 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,0676 kg CO2e / 1 Piece |

# Technical data sheet

## Cover plate, Telitank T4B, round installation opening for EKR device
## Item number: 7408244

### Dimensions




| | |
|---|---|
| Length | 77 mm |
| Width | 110 mm |
| Height | 2 mm |

### Technical data

| | |
|---|---|
| Application | On-floor tank |
| Number of CEE/Perilex openings | 0 |
| Number of triple openings | 0 |
| Number of single openings | 1 |
| Number of units | 1 |
| Number of oval openings | 0 |
| Number of square openings | 0 |
| Number of round openings | 0 |
| Number of double openings | 0 |
| Fastening type | Lockable |
| Labelling panel | no |
| Blanking lid | no |
| Suitable for labelling panel | no |
| Installation technology | Support clamp |
| ROHS-conformant | yes |