Technical data sheet

Height-adjustable cassette for inspection opening, RKN, brass

Item number: 7408972

"Blank" height-adjustable cassette for the creation of an inspection opening of nominal size 4. Installation of devices in duct systems, raised and cavity floors in interior dry or wet-care floors. Only suitable for smooth floor coverings.
For the installation of three UT4 universal supports for nine single devices with support ring/support clamp or 12 Modul 45® devices. 3 APMT5 cover plates can be installed.

IP 55

CuZn 37 Brass

Master data

Item number	7408972
Type	RKN3 9 MS 20
Description 1	Square cassette
Description 2	Blank lid
Manufacturer	OBO
Dimension	243x243x100
Material	Brass
Smallest sales unit	1
Unit of quantity	Piece
Weight	375 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	13,5476 kg CO2e / 1 Piece

Technical data sheet

Height-adjustable cassette for inspection opening, RKN, brass

Item number: 7408972

Dimensions



Length	243 mm
Width	243 mm
Height	105 mm
Dimension h	105 mm

Technical data

Number of installable devices	0
Number of cable outlets	0
Number of universal supports	3 x UT4
Cover version	Square
Cable outlet version	No cable outlet
Floor cut-out / Mounting opening	244x244
Floor care	Wet
Decouplable	no
Floor height, max.	150 mm
Floor height, min.	105 mm
Suitable for raised floor installation	yes
Suitable for cavity floor installation	yes
Suitable for underfloor box	250/350
Device support to accept mounting boxes	no
Length of installation dimensions	244 mm
Nominal size for device installation units	9
Height-adjustment range, max.	150 mm
Height-adjustment range, min.	105 mm
Standard	EN 50085-2-2
ROHS-conformant	Exempt
Protection rating (IP) when used	IP00
Protection rating (IP) when unused	IP55
Protection rating IK code	IK10
Heavy-duty version	no
Installation system type	UT4
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE
Floor covering thickness	20 mm