# Technical data sheet

## Frame cassette for tube body, RKF, nominal size 350-3, stainless steel
## Item number: 7409416

Frame cassette for tube body, for UZD350-3, for the installation of accessories in dry or wet-cleaned floors in interior areas. The tube body is not contained in the scope of delivery.

A2 Stainless steel

**Master data**

| | |
|---|---|
| Item number | 7409416 |
| Type | RKF3 V3 20 |
| Description 1 | Frame cassette |
| Description 2 | for tube |
| Manufacturer | OBO |
| Dimension | 383x383x20 |
| Material | Stainless steel 1.4301 |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 739 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 34,6875 kg CO2e / 1 Piece |

# Technical data sheet

## Frame cassette for tube body, RKF, nominal size 350-3, stainless steel
## Item number: 7409416

### Dimensions




| | |
|---|---|
| Dimension A | 424 mm |
| Dimension B | 388 mm |
| Dimension C | 382 mm |
| Dimension h | 20 mm |

### Technical data

| | |
|---|---|
| Number of cable outlets | 1 |
| Cable outlet version | Lowerable tube body |
| Floor care | Wet |
| Suitable for | Underfloor socket structure |
| Suitable for underfloor box | 350 |
| Device support to accept mounting boxes | no |
| ROHS-conformant | yes |
| Protection rating (IP) when used | IP20 |
| Protection rating (IP) when unused | IP44 |
| Vertical load, large area | to 3,000 N |
| Vertical load, small area | to 3,000 N |
| Floor covering thickness | 18 mm |