# Technical data sheet

## Height-compensation kit ASH 250-4 240

## Item number: 7410134

Height-compensation kit for UZD250-4 underfloor boxes with a construction height of 160 to 240 mm for construction-side raising of the UZD.

St Steel

FS Strip galvanised

### Master data

| | |
|---|---|
| Item number | 7410134 |
| Type | ASH 250-4 240 |
| Description 1 | Height compensation set |
| Description 2 | for UZD 250-4 |
| Manufacturer | OBO |
| Dimension | 350x103x46 |
| Material | Steel |
| Surface | Strip galvanised |
| Surface standard | DIN EN 10346 |
| Smallest sales unit | 1 |
| Unit of quantity | Packaging unit |
| Weight | 91 kg |
| Weight unit | kg/100 PUs |
| CO2 Footprint (GWP) Cradle-to-Gate | 2,767 kg CO2e / 4 Piece |

# Technical data sheet

## Height-compensation kit ASH 250-4 240

## Item number: 7410134

### Dimensions




| | |
|---|---|
| Length | 350 mm |
| Width | 103 mm |
| Dimension A | 350 mm |
| Dimension B | 103 mm |
| Dimension l | 47.5 mm |

### Technical data

| | |
|---|---|
| Version for | Square |
| Floor plate | no |
| Lowerable to be flush-floor | no |
| Seal installation option | no |
| Installation opening for on-floor tank | no |
| Decouplable | no |
| Screed height, max. | 240 mm |
| Screed height, min. | 160 mm |
| For pipe connection | no |
| Suitable for raised floor installati-on | no |
| Suitable for screed-flush closed underfloor ducts | no |
| Suitable for screed-covered un-derfloor ducts | yes |
| Suitable for cavity floor installation | no |
| Suitable for underfloor ducts | no |
| Trunking width, max. | 250 mm |
| Trunking width, min. | 190 mm |
| Minimum screed height | 160 |
| Height-adjustment range, max. | 240 mm |
| Height-adjustment range, min. | 160 mm |
| ROHS-conformant | yes |