# Technical data sheet

## Trunking unit for GES9, height 40−140 mm

## Item number: 7424200



Ready-to-mount screed-flush trunking unit for cable routing, consisting of three system covers, two side profiles with attached flexible side wall made of metallic mesh, floor covering contact profiles with H = 3 mm. For dry interior rooms with dry-care floors. Also suitable for wet-care floors with appropriate system accessories. The scope of delivery contains six height-adjustable fastening brackets, six screed ties and three lid butt seals for nominal trunking widths 200, 300 and 400 or six lid butt supports for trunking widths 500 and 600. The essential levelling units (please observe adjustment height) for the lid butt supports 400, 500 and 600 are not contained in the scope of supply, please order separately. On delivery, the trunking lids are screwed on.
With three (for nominal trunking width 400, L = 800 mm) or six device installation lids (for nominal trunking widths 500 and 600, L = 400 mm) each with one installation opening for a square installation unit of nominal size 9.

| | |
|---|---|
| St | Steel |
| FS | Strip galvanised |

### Master data

| | |
|---|---|
| Item number | 7424200 |
| Type | OKA-G40040140D9 |
| Description 1 | Flushfloor trunking unit |
| Description 2 | for service unit GES9 |
| Manufacturer | OBO |
| Dimension | 2400x400x140 |
| Material | Steel |
| Surface | Strip galvanised |
| Surface standard | DIN EN 10346 |
| Smallest sales unit | 2.4 |
| Unit of quantity | Metre |
| Weight | 1431.7 kg |
| Weight unit | kg/100 m |
| CO2 Footprint (GWP) Cradle-to-Gate | 62,4694 kg CO2e / 1 Meter |

### Dimensions




| | |
|---|---|
| Length | 2,400 mm |
| Width | 400 mm |

# Technical data sheet

## Trunking unit for GES9, height 40−140 mm

## Item number: 7424200

### Technical data

| | |
|---|---|
| Mounting opening cover | yes |
| Covers | 3 |
| Number of planned flush-mount units | 3 |
| Mounting system fastening type | Floor |
| Floor plate | no |
| Cover fastening, locking | no |
| Seal installation option | yes |
| Installation opening for on-floor tank | no |
| Decouplable | yes |
| Suitable for expansion joint | no |
| Mesh wall | yes |
| Trunking height, max. | 140 mm |
| Duct height, min. | 40 mm |
| Cover material thickness | 4 |
| Minimum screed height | 40 |
| With connection opening | yes |
| With equipotential bonding | no |
| With separating retainer | no |
| With overhang | yes |
| Mounting opening | For service outlet |
| Mounting opening | Square |
| Nominal size for device installati-on units | 9 |
| Height-adjustment range, max. | 140 mm |
| Height-adjustment range, min. | 40 mm |
| Removable cover | yes |
| ROHS-conformant | yes |