Technical data sheet

UDHOME4 floor box, with universal support UT3 45 3, triple NF, stainless steel
Item number: 7427224

Square floor box for use in dry-cleaned cavity and screed floors for indoor use. Installation housing with pre-marked insertion openings for pipes (M25). Cover adjustable to top edge of floor covering using four height-adjustment supports. 15 mm floor covering recess in the hinged cover. The minimum installation depth is 95 mm, the height-adjustment range + 30 mm.

The scope of delivery contains two universal supports UT3 45 3 and one triple NF socket. Up to three additional M45 devices can be installed.

A2 Stainless steel

Master data

Item number	7427224
Type	UDHOME4 2V UT N
Description 1	Floor box, complete
Description 2	triple NF socket
Manufacturer	OBO
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	413 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	18,2812 kg CO2e / 1 Piece

Technical data sheet

UDHOME4 floor box, with universal support UT3 45 3, triple NF, stainless steel
Item number: 7427224

Dimensions





Length	202 mm
Width	202 mm

Technical data

Number of mounting boxes	2
Cover version	Square
Cable outlet version	Swivellable cord outlet
Equipment	2 UT3, triple LF socket
Floor covering protection frame	no
Cover version	Floor covering recess
Screed height, max.	110 mm
Screed height, min.	95 mm
Floor height, max.	125 mm
Floor height, min.	95 mm
Suitable for raised floor installation	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
Length of external dimensions	199 mm
Length of installation dimensions	202 mm
With floor covering recess	yes
Height-adjustment range, max.	125 mm
Height-adjustment range, min.	95 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Opening mechanism	Handle
Floor covering thickness	15 mm