Technical data sheet

UDHOME9 floor box, freely equippable, stainless steel

Item number: 7427324

Square floor box for use in dry-cleaned cavity and screed floors in indoor areas. Installation housing with pre-marked insertion openings for pipes (M25). Empty housing for up to three UT4 universal supports for up to 12 Modul 45 ® devices. Cover adjustable to top edge of floor covering using four height-adjustment supports. The minimum installation depth is 95 mm, the height-adjustment range + 30 mm.
Surfaces visible in the floor covering made of stainless steel.

A2 Stainless steel

Master data

Item number	7427324
Type	UDHOME9 2V
Description 1	Floor box, complete
Description 2	empty
Manufacturer	OBO
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	470 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	23,0975 kg CO2e / 1 Piece

Technical data sheet

UDHOME9 floor box, freely equippable, stainless steel

Item number: 7427324

Dimensions





Length	246 mm
Width	246 mm

Technical data

Cable outlet version	Swivellable cord outlet
Equipment	Empty housing
Cover version	Floor covering recess
Screed height, max.	110 mm
Screed height, min.	95 mm
Floor height, max.	125 mm
Floor height, min.	95 mm
Suitable for raised floor installati-on	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered un-derfloor ducts	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
Length of external dimensions	243 mm
Length of installation dimensions	246 mm
With floor covering recess	yes
Height-adjustment range, max.	125 mm
Height-adjustment range, min.	95 mm
ROHS-conformant	Exempt
Protection rating (IP) when used	IP20
Protection rating (IP) when unu-sed	IP40
Protection rating IK code	IK10
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Opening mechanism	Handle
Floor covering thickness	15 mm