
Technical data sheet

Cover for triple accessory mounting box for WDK trunking, trunking height 150 mm
Item number: 6169422



Cover section, triple, for device installation in WDK trunking in conjunction with the device installation socket, type 2390.

PVC Polyvinylchloride


Master data

Item number	6169422
Type	D2-3 150CW
Description 1	Cover
Description 2	for triple device installation
Manufacturer	OBO
Dimension	150x300mm
Colour	Cream; RAL 9001
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	9.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,3724 kg CO2e / 1 Piece

Technical data sheet

Cover for triple accessory mounting box for WDK trunking, trunking height 150 mm
Item number: 6169422

Dimensions



Length	300 mm

Technical data

Maintain electrical functions	no
Halogen-free	no
ROHS-conformant	yes
Protection rating	IP30
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C