

# Technical data sheet

## Spreading anchor, plastic

Item number: 2347723



Nylon spreading anchor for mounting components on walls and ceilings. Suitable for solid building materials such as concrete, sand-lime brick and masonry. With pre-fixing of the screw for easy overhead mounting. The given load values are valid for wood screws with the specified diameter.



**PA** Polyamide

### Master data

|                     |                  |
|---------------------|------------------|
| Item number         | 2347723          |
| Type                | SX Plus 6x30     |
| Description 1       | Spreading anchor |
| Manufacturer        | OBO              |
| Dimension           | 6x30             |
| Colour              | Light grey       |
| Material            | Polyamide        |
| Smallest sales unit | 100              |
| Unit of quantity    | Piece            |
| Weight              | 0.061 kg         |
| Weight unit         | kg/100 pc.       |


# Technical data sheet

Spreading anchor, plastic

Item number: 2347723



## Dimensions



|             |       |
|-------------|-------|
| Length      | 30 mm |
| Dimension D | 6 mm  |
| Dimension L | 30 mm |

# Technical data sheet

## Spreading anchor, plastic

Item number: 2347723



### Technical data

|                                          |                                                                                                 |
|------------------------------------------|-------------------------------------------------------------------------------------------------|
| Version for                              | Spreading anchor                                                                                |
| Concrete Frat                            | 650                                                                                             |
| Drill hole depth                         | 40 mm                                                                                           |
| Drill hole diameter, max.                | 6 mm                                                                                            |
| Drill hole diameter, min.                | 6 mm                                                                                            |
| Suitable for fastening with cable ties   | no                                                                                              |
| Suitable for gas concrete                | yes                                                                                             |
| Suitable for screw diameter, max.        | 5 mm                                                                                            |
| Suitable for screw diameter, min.        | 4 mm                                                                                            |
| Suitable for hexagonal wood screw        | yes                                                                                             |
| Hollow brick Hlz12 Frat                  | 150                                                                                             |
| Porous calcareous sandstone KSL12 Fempf. | 300                                                                                             |
| Solid calcareous sandstone KSL12 Frat    | 650                                                                                             |
| With edge                                | yes                                                                                             |
| With bolts                               | no                                                                                              |
| Porous concrete P2 Fempf.                | 70                                                                                              |
| Porous concrete P4 Fempf.                | 200                                                                                             |
| ROHS-conformant                          | yes                                                                                             |
| Full brick Mz12 Frat                     | 350                                                                                             |
| Suitable for material                    | Calcareous sandstone Porous concrete Concrete Gas concrete Plasterboard Full brick Hollow brick |
| Mounting type, anchor, tie               | Push-through mounting Pre-mounting                                                              |