

OBO BETTERMANN Holding GmbH & Co. KG
Postfach 1120 • D-58694 Menden
Hüingser Ring 52 • D-58710 Menden

Tel. 0 23 73 / 89-0
Fax 0 23 73 / 89-1238
E-Mail: info@obo.de
www.obo.de

OBO Bettermann Hungary Kft.
Bugyi, Alsóráda 2, H-2347



Dear customer,

as the manufacturer, we hereby declare that the following product

Product Name: Clamp clip 2056

Type Name: BS-H1-M-34 FT

Article Number: 1186029

manufactured by our company, OBO Bettermann Hungary Kft. complies with the requirements of the short-circuit withstanding requirements as specified in 9.5 part of IEC 61914:2021. The tested arrangement can withstand one short-circuit with the values/characteristics defined by the manufacturer:

Peak short-circuit current:	40 kA
Duration of short-circuit current:	100 ms
Diameter of the applied cables:	34.5 mm
Arrangement of the cables:	flat
Cable center spacing:	100 mm
Linear spacing of the clips:	300 mm

Due to the structure of the standard, the test carried out with the cable defined above also applies to the further versions of the product portfolio used for other cable diameters in the same arrangement:

Type Name:	BS-H1-M-12 FT / BS-H1-M-16 FT / BS-H1-M-22 FT / BS-H1-M-28 FT / BS-H1-M-40 FT / BS-H1-M-46 FT / BS-H1-M-52 FT / BS-H1-M-58 FT / BS-H1-M-64 FT / BS-H1-M-70 FT / BS-H1-M-76 FT / BS-H1-M-82 FT / BS-H1-M-90 FT / BS-H1-M-100 FT
Article Number:	1186002 / 1186009 / 1186016 / 1186022 / 1186036 / 1186042 / 1186049 / 1186056 / 1186062 / 1186069 / 1186076 / 1186082 / 1186089 / 1186097

Kind Regards

Bugyi, 27.06.2025


i.V. Markus Mende
Director of PPM


i.V. Kevin Kutschelis
Leader of R&D


i.A. Gábor Tóth
Product Manager

Handelsregister:
Amtsgericht Arnsberg · HRA 4854
Sitz: Menden · UST-IdNr. DE 811 792 270
Pers. haft. Gesellschafterin:
OBO Bettermann Beteiligungs-GmbH
Amtsgericht Arnsberg · HRB 4833
Sitz: Menden

Geschäftsführer:
Ulrich Bettermann
Prof. Dr. Robert Gröning
Lajos Hernádi
Christoph Palausch

Bankverbindungen:
Commerzbank AG
Deutsche Bank AG
HSBC Trinkaus & Burkhardt AG
Mendener Bank eG
Sparkasse UnnaKamen
UniCredit Bank AG

BIC: COBADEFF445	IBAN: DE95 4454 0022 0570 5744 00
BIC: DEUTDE33HAN	IBAN: DE44 4457 0004 0407 6691 00
BIC: TUBDDE33HAN	IBAN: DE62 3003 0880 0370 2320 08
BIC: GENODEM33HAN	IBAN: DE65 4476 1312 0330 0076 00
BIC: WELADED1UNN	IBAN: DE35 4435 0060 1000 4245 96
BIC: HYVEDE33HAN	IBAN: DE83 4402 0090 0021 4268 73