


Technical data sheet

Cone cable gland, metric thread, light grey

Item number: 2035367



Standard cable gland, shape A, to DIN 46320 with simple NR/SBR sealing ring with metric connection thread to IEC 423.

Protection rating: with connection thread sealing ring IP65, without connection thread sealing ring IP54.

Note: Only tighten polystyrene cable glands lightly due to the risk of stress crack formation.
Shock-resistant



PS Polystyrene

Master data

Item number	2035367
Type	106 M 40 PS
Description 1	Cable gland
Manufacturer	OBO
Dimension	M40
Colour	Light grey; RAL 7035
Material	Polystyrene
Smallest sales unit	10
Unit of quantity	Piece
Weight	4.973 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,2321 kg COe / 1 Piece


Technical data sheet

Cone cable gland, metric thread, light grey

Item number: 2035367



Dimensions



Length	58 mm
Width	61 mm
Height	52.5 mm
Dimension D1	33 mm
Dimension D2	60 mm
Dimension D3	38.4 mm
Dimension D4	33 mm
Dimension G	M40x1,5 mm
Dimension L max.	43 mm
Dimension L1	12 mm
Dimension L2	24 mm
Dimension L3	8 mm
Dimension L4	17 mm

Technical data

Type of seal	Sealing ring
Version for	Straight
Bend protection	no
Sealing area D, max.	33 mm
Sealing area D, min.	25 mm
explosion-proof	no
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
Thread	M40 x 1,5
Thread type	Metric
Thread length	12 mm
Nominal thread size	40
Fibre-glass reinforced	no
Halogen-free	yes
Sealing insert, multiple	no
With locknut	no
Impact-resistant	yes
WAF 1	53 mm
WAF 2	50 mm
Protection rating	IP65
Splittable gland	no
Strain relief option	no