

# Technical data sheet

## Cone cable gland, PG thread, strain relief, nickel-plated

Item number: 2046210



Cable gland with centrally acting transverse clip strain relief in the pressure screw, bend protection of movable cables through strongly rounded pressure screw.

With Pg connection thread to DIN 40430.

Pressure rings made of electrogalvanised and transparently passivated steel. NR/SBR sealing ring.

Protection rating: with connection thread sealing ring IP 65, without connection thread sealing ring IP 54.

With hexagonal intermediate support (similar to shape C 4 to DIN 46320).

\* Prices according to DEL notation.



Brass



Nickel-plated

### Master data

Item number	2046210
Type	159 MS PG21
Description 1	Cable gland
Description 2	with outside hexagonal
Manufacturer	OBO
Dimension	PG21
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	7.59 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,2112 kg COe / 1 Piece


# Technical data sheet

## Cone cable gland, PG thread, strain relief, nickel-plated

Item number: 2046210



### Dimensions



Dimension E	37 mm
Dimension L max.	32 mm
Dimension L1	7 mm
Dimension L2	15 mm
Dimension L3	13.3 mm

### Technical data

Type of seal	Sealing ring
Bend protection	no
Sealing area D, max.	19 mm
Sealing area D, min.	17 mm
explosion-proof	no
Flat cable gland	no
For Ex zone	Without
Thread	Pg 21
Thread type	PG
Thread length	7 mm
Fibre-glass reinforced	no
Halogen-free	no
Sealing insert, multiple	no
With locknut	no
Impact-resistant	no
WAF	30
WAF 1	30 mm
WAF 2	33 mm
Protection rating	IP65
Strain relief option	yes