

# Technical data sheet

## Screw plug, PG thread

Item number: 2033488



Screw plug in accordance with DIN 46320, with PG thread to DIN 40430. Protection rating IP54, IP68 (5 bar/1h) possible in conjunction with sealing ring type 171.



**PS** Polystyrene

### Master data

|                                    |                        |
|------------------------------------|------------------------|
| Item number                        | 2033488                |
| Type                               | 108 PG48               |
| Description 1                      | Screw plug             |
| Manufacturer                       | OBO                    |
| Dimension                          | PG48                   |
| Colour                             | Light grey; RAL 7035   |
| Material                           | Polystyrene            |
| Smallest sales unit                | 25                     |
| Unit of quantity                   | Piece                  |
| Weight                             | 1.832 kg               |
| Weight unit                        | kg/100 pc.             |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,078 kg COe / 1 Piece |


# Technical data sheet

## Screw plug, PG thread


Item number: 2033488



### Dimensions



|             |       |
|-------------|-------|
| Dimension D | 73 mm |
| Dimension L | 12 mm |



### Technical data

|                               |         |
|-------------------------------|---------|
| explosion-proof               | no      |
| For Ex zone gas               | Without |
| For Ex zone dust              | Without |
| Thread                        | Pg 48   |
| Thread type                   | PG      |
| Nominal thread size metric/PG | 48      |
| Thread increase               | 1.59 mm |
| Fibre-glass reinforced        | no      |
| Halogen-free                  | yes     |
| Unstable torque               | 5 Nm    |
| Impact-resistant              | yes     |
| Protection rating             | IP54    |