

Technical data sheet

Adapter expansion M - PG

Item number: 2088318



The areas of application for brass cable glands range from junction boxes as a distribution/connection box up to large industrial applications for safe floor routing to switchgear cabinets with a control and distribution function. For high mechanical requirements, OBO can offer the entire family with long and short connection threads and locknuts with a metric and Pg thread.

CE M Pg

CuZn
37

Brass

N

Nickel-plated

Master data

Item number	2088318
Type	165 ADA M20-PG16
Description 1	Adapter
Description 2	M - PG
Manufacturer	OBO
Dimension	M20-PG16
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	20
Unit of quantity	Piece
Weight	1.65 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0461 kg CO2e / 1 Piece


Technical data sheet

Adapter expansion M - PG

Item number: 2088318



Dimensions



Dimension D	24 mm
Dimension L	19.5 mm
Dimension L1	6 mm
Dimension L2	13.5 mm

Technical data

explosion-proof	no
Thread type: External thread	Metric
Thread type: Internal thread	PG
Thread dimension, metric, external	20
Thread dimension, PG, internal	16
Nickel-plated	yes