

# Technical data sheet

## Reduction, PG thread

Item number: 2089157



Reduction (Part H) to DIN 46320, with Pg thread to DIN 40430, as a transition from a PG thread hole to a smaller cable gland.

\* Prices according to DEL notation.



**CuZn**  
37 Brass

**N** Nickel-plated

### Master data

Item number	2089157
Type	167 R MS PG16-9
Description 1	Reduction
Manufacturer	OBO
Dimension	PG16-PG9
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	50
Unit of quantity	Piece
Weight	1.73 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,0442 kg COe / 1 Piece


# Technical data sheet

## Reduction, PG thread

Item number: 2089157



### Dimensions



Dimension D	24 mm
Dimension L1	6.5 mm
Dimension L2	3 mm

### Technical data

explosion-proof	no
Thread type: External thread	PG
Thread type: Internal thread	PG
Thread length	6.5 mm
Thread dimension, PG, external	16
Thread dimension, PG, internal	9
Nickel-plated	yes