


Technical data sheet

Reduction, PG thread

Item number: 2089025



Reduction (Part H) to DIN 46320, with Pg thread to DIN 40430, as a transition from a PG thread hole to a smaller cable gland.
* Prices according to DEL notation.



CuZn
37 Brass

N Nickel-plated

| Master data | | |
|-----------------------------------|-------------------------|--|
| Item number | 2089025 | |
| Type | 167 R MS PG9-7 | |
| Description 1 | Reduction | |
| Manufacturer | OBO | |
| Dimension | PG9-PG7 | |
| Material | Brass | |
| Surface | Nickel-plated | |
| Surface standard | | |
| Smallest sales unit | 50 | |
| Unit of quantity | Piece | |
| Weight | 0.43 kg | |
| Weight unit | kg/100 pc. | |
| CO Footprint (GWP) Cradle-to-Gate | 0,0119 kg COe / 1 Piece | |


Technical data sheet

Reduction, PG thread

Item number: 2089025



Dimensions



| | |
|--------------|--------|
| Dimension D | 17 mm |
| Dimension L1 | 6 mm |
| Dimension L2 | 2.5 mm |

Technical data

| | |
|--------------------------------|------|
| explosion-proof | no |
| Thread type: External thread | PG |
| Thread type: Internal thread | PG |
| Thread length | 6 mm |
| Thread dimension, PG, external | 9 |
| Thread dimension, PG, internal | 7 |
| Nickel-plated | yes |