

# Technical data sheet

## Electrical insulating and sealing compound

Item number: 2340038



In rods.

Permanently elastic, fibre-free sealing kit on a polymer and a mineral basis to fill cavities in installations, e.g. cable glands or similar components, to prevent the entry of dirt and water.

Colour: Natural

Characteristics of the sealing kit:

- Halogen-, acid- and silicone-free
  - Can also be processed at low temperatures
  - Permanent heat resistance to +80 °C
  - Corrosion-resistant
  - Low water consumption
  - Good insulation properties
  - Puncture strength 16 kV/mm to VDE 0291 Part 2
  - Can be stored almost indefinitely
- Characteristics of the sealing kit:
- Halogen, acid and silicone-free
  - Can also be processed at low temperatures
  - Permanent heat resistance to +80 °C
  - Corrosion-resistant
  - Low water consumption
  - Good insulation properties
  - Puncture strength 16 kV/mm to VDE 0291 Part 2
  - Can be stored almost indefinitely

### Master data

Item number	2340038
Type	115 GR-GN
Description 1	Elec. insulation + sealing kit
Manufacturer	OBO
Dimension	ca.100g
Colour	Natural
Smallest sales unit	10
Unit of quantity	Piece
Weight	11.02 kg
Weight unit	kg/100 pc.

# Technical data sheet

Electrical insulating and sealing compound

Item number: 2340038



## Technical data

Version for	Mineral base
Packaging	Rod