


Technical data sheet

Hat profile rail, perforated GTP

Item number: 1115456



Hat profile rail 35 x 15 mm similar to DIN EN 60715 (formerly DIN EN 50022), but with material thickness 1.5 mm.



- St

Steel
- GTP

Electrogalvanized, transparently passivated

Master data		
	Item number	1115456
	Type	2069 15 1.5 GTPL
	Description 1	Top hat rail
	Description 2	perforated, 1.5 mm thick
	Manufacturer	OBO
	Dimension	2000x35x15
	Material	Steel
	Surface	Electrogalvanized, transparently passivated
	Surface standard	
	Smallest sales unit	2
	Unit of quantity	Metre
	Weight	64 kg
	Weight unit	kg/100 m
	CO Footprint (GWP) Cradle-to-Gate	1,1932 kg COe / 1 Meter


Technical data sheet

Hat profile rail, perforated GTP


Item number: 1115456



Dimensions



Length	2,000 mm
Width	35 mm
Height	15 mm



Technical data

Version for	Perforated
Version, rails	Support rail DIN EN 60715
Drill hole spacing, centre	25 mm
Bundle	20 m
Hole shape (ETIM)	Long slot
Material thickness	1.5 mm