

Technical data sheet

Dolü branch terminals, open on one side

Item number: 2055201



Terminals made of brass, screws of steel, galvanised and transparently passivated, 12-pole, strip separable into individual terminals, only open on one side. Closed on one side, captive upwards screw.

Nominal cross-section $2.5 \div \text{mm}^2$.

Nominal voltage 250 V.

Nominal current 24 A.

Max. connectable cross-sections per terminal: $4 \times 2.5 \text{ mm}^2$, $5 \times 1.5 \text{ mm}^2$ or $6 \times 1 \text{ mm}^2$.

Delivery sorted by colour: 3 black, 2 blue, 3 yellow-green, 1 brown and 1 grey strip in each packaging unit.



PA Polyamide

Master data

| | |
|-----------------------------------|-------------------------|
| Item number | 2055201 |
| Type | 70 S |
| Description 1 | Dolü branch terminal |
| Description 2 | closed on one side |
| Manufacturer | OBO |
| Dimension | 2.5 mm^2 |
| Colour | (sorted) |
| Material | Polyamide |
| Smallest sales unit | 10 |
| Unit of quantity | Piece |
| Weight | 2.852 kg |
| Weight unit | kg/100 pc. |
| CO Footprint (GWP) Cradle-to-Gate | 0,2561 kg COe / 1 Piece |


Technical data sheet

Dolü branch terminals, open on one side

Item number: 2055201



Dimensions



| | |
|--------|----------|
| Length | 129.6 mm |
| Width | 12 mm |
| Height | 17.5 mm |

Technical data sheet

Dolü branch terminals, open on one side

Item number: 2055201



Technical data

| | |
|--------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Closing plate required | no |
| Connectable conductor cross-section, single-wire, max. | 2.5 mm ² |
| Connectable conductor cross-section, single-wire, min. | 1 mm ² |
| Connection position | Side |
| No. of terminals | 12 |
| Number of screwless terminals per pole | 1 |
| Version of electrical connection 1 | Screw connection |
| Drill hole spacing, centre | 11 mm |
| Explosion-tested version | no |
| Suitable for flexible conductors | yes |
| Suitable for solid conductors | no |
| Suitable for multi-wire conductors | yes |
| Halogen-free | yes |
| Insulation material | Thermoplast |
| Mounting type | Direct mounting |
| Nominal cross-section, min. | 2.5 mm ² |
| Nominal voltage | 250 V |
| Nominal current | 24 A |
| Pole number | 12 |
| Cross-section | Max. connectable cross-sections per terminal: 4 x 2.5 mm ² , 5 x 1.5 mm ² or 6 x 1 mm ² mm ² |
| Transparent | no |