


Technical data sheet

Screw-in nipple, PG thread, with perforation membrane

Item number: 2032562



With perforation membrane, the opening D is pre-marked, but closed.

Grip seal to screw into PG thread to DIN 40430.

With self-sealing cone at the end of the thread, therefore no connection thread sealing ring required. Protection rating achievable with careful mounting: IP54.
With perforation membranes, the opening D is pre-marked, but closed.



PE Polyethylene

Master data

| | |
|------------------------------------|-------------------------|
| Item number | 2032562 |
| Type | 90 PG29 DSMB |
| Description 1 | Screw-in nipple |
| Description 2 | with puncture membrane |
| Manufacturer | OBO |
| Dimension | PG29 |
| Colour | Light grey; RAL 7035 |
| Material | Polyethylene |
| Smallest sales unit | 25 |
| Unit of quantity | Piece |
| Weight | 0.563 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,0258 kg COe / 1 Piece |


Technical data sheet

Screw-in nipple, PG thread, with perforation membrane

Item number: 2032562



Dimensions



| | |
|--------------|---------|
| Dimension D | 15 mm |
| Dimension E | 40 mm |
| Dimension L1 | 11.5 mm |
| Dimension L2 | 6 mm |

Technical data

| | |
|-------------------|---------|
| Thread length | 11.5 mm |
| Size | Pg 29 |
| Halogen-free | yes |
| WAF | 37 |
| Protection rating | IP54 |