


# Technical data sheet

## Pressure clip for 16 cables, flame resistant

Item number: 2204916



Flame-resistant version, specially for use in suspended ceilings.

Thermoplast. Polyester, stone grey RAL 7030, flame-resistant to VDE 0471/DIN IEC 695 Part 2-1, Test temperature 960 °C, respectively V-O to UL 94, halogen-free.

Clamping height: 9 mm, with spacer 13 mm.

Fastening hole: 6 mm Ø.

2033/F for max. 16 conductors NYM 3 x 1.5 mm<sup>2</sup>



**PBPT** Polybutylene terephthalate

### Master data

|                                    |                            |
|------------------------------------|----------------------------|
| Item number                        | 2204916                    |
| Type                               | 2033 F                     |
| Description 1                      | Pressure clip              |
| Manufacturer                       | OBO                        |
| Dimension                          | 2x8 NYM3x1,5               |
| Colour                             | Stone grey; RAL 7030       |
| Material                           | Polybutylene terephthalate |
| Smallest sales unit                | 25                         |
| Unit of quantity                   | Piece                      |
| Weight                             | 2.588 kg                   |
| Weight unit                        | kg/100 pc.                 |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,0048 kg COe / 1 Piece    |


# Technical data sheet

## Pressure clip for 16 cables, flame resistant

Item number: 2204916



### Dimensions



### Technical data

|                               |                                                           |
|-------------------------------|-----------------------------------------------------------|
| No. of conductors NYM 3 x 1.5 | 16                                                        |
| Flame-resistant version       | yes                                                       |
| Flame-resistant               | Acc. to VDE 0471/DIN 695 Part 2-1, test temperature 750°C |
| Maintain electrical functions | no                                                        |
| Halogen-free                  | yes                                                       |
| With anchor                   | no                                                        |