

# Technical data sheet

## Double trough, metal DD

Item number: 1199714



Metallic double trough as intermediate layer between two or three cables within a clamp clip.



- St** Steel
- DD** Strip galvanised zinc/aluminium, Double Dip

| Master data                       |                                             |
|-----------------------------------|---------------------------------------------|
| Item number                       | 1199714                                     |
| Type                              | 2058 M2 16 DD                               |
| Description 1                     | Double trough                               |
| Manufacturer                      | OBO                                         |
| Dimension                         | 12-16mm                                     |
| Material                          | Steel                                       |
| Surface                           | Strip galvanised zinc/aluminium, Double Dip |
| Surface standard                  | DIN EN 10346                                |
| Smallest sales unit               | 50                                          |
| Unit of quantity                  | Piece                                       |
| Weight                            | 1.8 kg                                      |
| Weight unit                       | kg/100 pc.                                  |
| CO Footprint (GWP) Cradle-to-Gate | 0,0554 kg COe / 1 Piece                     |


# Technical data sheet

## Double trough, metal DD


Item number: 1199714



### Dimensions



|             |         |
|-------------|---------|
| Dimension B | 21.5 mm |
| Dimension H | 5.4 mm  |
| Dimension L | 35 mm   |



### Technical data

|                                  |               |
|----------------------------------|---------------|
| Counter-trough/clip version      | Double trough |
| Suitable for max. cable diameter | 16 mm         |
| Clamping range D, max.           | 16 mm         |
| Clamping range D, min.           | 12 mm         |