

# Technical data sheet

Hat profile rail 15 x 5 mm

Item number: 1115270



Hat profile rail 15 x 5 mm to DIN EN 60715 (formerly DIN EN 50045).



Steel



Electrogalvanized, transparently passivated

## Master data

|                                   |                                             |
|-----------------------------------|---------------------------------------------|
| Item number                       | 1115270                                     |
| Type                              | 46277 T160 Q GTP                            |
| Description 1                     | Top hat rail                                |
| Description 2                     | for terminal block fastening                |
| Manufacturer                      | OBO                                         |
| Dimension                         | 99x15x7,4                                   |
| Material                          | Steel                                       |
| Surface                           | Electrogalvanized, transparently passivated |
| Surface standard                  |                                             |
| Smallest sales unit               | 10                                          |
| Unit of quantity                  | Piece                                       |
| Weight                            | 1.77 kg                                     |
| Weight unit                       | kg/100 pc.                                  |
| CO Footprint (GWP) Cradle-to-Gate | 0,0434 kg COe / 1 Piece                     |


# Technical data sheet

Hat profile rail 15 x 5 mm

Item number: 1115270



## Dimensions



|        |       |
|--------|-------|
| Length | 99 mm |
| Width  | 15 mm |
| Height | 5 mm  |

## Technical data

|                    |                                     |
|--------------------|-------------------------------------|
| Version for        | For T160 crosswise +T100 lengthwise |
| Version, rails     | Support rail DIN EN 60715           |
| Hole shape (ETIM)  | Without                             |
| Material thickness | 1 mm                                |