


# Technical data sheet

## Dolü branch terminals, open on both sides, 12-pole

Item number: 2055023



Sorted in colours black, brown, blue and yellow-green.

Terminals made of brass, screws of steel, galvanised and transparently passivated, 12-pole, strip separable into individual terminals, open on both sides.

Captive upwards screw.

Nominal cross-section  $2.5 \div \text{mm}^2$ .

Nominal voltage 380 V.

Nominal current 16 A.

Max. connectable cross-sections per terminal:  $4 \times 2.5 \text{ mm}^2$ ,  $5 \times 1.5 \text{ mm}^2$  or  $6 \times 1 \text{ mm}^2$ .

Delivery sorted by colour: 5 black, 2 blue, 2 yellow-green and 1 brown strip in each packaging unit.



PA Polyamide

### Master data

Item number	2055023
Type	70 VDE
Description 1	Dolü branch terminal
Description 2	colours sorted
Manufacturer	OBO
Dimension	$2.5 \text{ mm}^2$
Colour	(sorted)
Material	Polyamide
Smallest sales unit	10
Unit of quantity	Piece
Weight	2.5 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,1012 kg COe / 1 Piece


# Technical data sheet

## Dolü branch terminals, open on both sides, 12-pole

Item number: 2055023



### Dimensions



Length	122 mm
Width	15 mm
Height	17 mm

### Technical data

Closing plate required	no
Connectable conductor cross-section, single-wire, max.	2.5 mm <sup>2</sup>
Connectable conductor cross-section, single-wire, min.	1 mm <sup>2</sup>
Connection position	Side
No. of terminals	12
Number of screwless terminals per pole	1
Version of electrical connection 1	Screw connection
Drill hole spacing, centre	10.25 mm
Explosion-tested version	no
Suitable for flexible conductors	yes
Suitable for solid conductors	no
Suitable for multi-wire conductors	yes
Halogen-free	yes
Insulation material	Thermoplast
Mounting type	Direct mounting
Nominal cross-section, min.	2.5 mm <sup>2</sup>
Nominal voltage	380 V
Nominal current	16 A
Pole number	12
Cross-section	Max. connectable cross-sections per terminal: 4 x 2.5 mm <sup>2</sup> , 5 x 1.5 mm <sup>2</sup> or 6 x 1 mm <sup>2</sup> mm <sup>2</sup>
Transparent	no