

# Technical data sheet

## End piece Signa Base ES 70130

Item number: 6132777



End piece as a fitting for the Signa Base device installation trunking.  
For a clean end to the trunking system.



Polycarbonate/Acrylnitrile-butadiene-styrene

### Master data

|                     |                                              |
|---------------------|----------------------------------------------|
| Item number         | 6132777                                      |
| Type                | BRK ES70130 cws                              |
| Description 1       | End piece                                    |
| Description 2       | SIGNA BASE 70x130 9001                       |
| Manufacturer        | OBO                                          |
| Colour              | Cream; RAL 9001                              |
| Material            | Polycarbonate/Acrylnitrile-butadiene-styrene |
| Smallest sales unit | 1                                            |
| Unit of quantity    | Piece                                        |
| Weight              | 5.69 kg                                      |
| Weight unit         | kg/100 pc.                                   |


# Technical data sheet

End piece Signa Base ES 70130

Item number: 6132777



## Dimensions



|        |        |
|--------|--------|
| Length | 34 mm  |
| Width  | 137 mm |
| Height | 73 mm  |

## Technical data

|                                   |             |
|-----------------------------------|-------------|
| Version for                       | Symmetrical |
| Fastening type                    | Lockable    |
| for duct width                    | 130 mm      |
| for trunking height               | 70 mm       |
| Suitable for                      | Left/right  |
| Halogen-free                      | yes         |
| Cut lamination                    | yes         |
| Protection rating                 | IP40        |
| Protective film                   | no          |
| Protection rating IK code         | IK07.       |
| Permitted temperature range, max. | 60 °C       |
| Permitted temperature range, min. | -5 °C       |