

Technical data sheet

PYROLINE® Con D BSK I90/E30 fire protection duct

Item number: 7215144



Fire protection duct made from water and frost-proof fibreglass lightweight concrete of building material class A1 according to EN 13501-1 for fireproof laying of cables in rescue and emergency routes, and for the maintenance of electrical functionality of safety-relevant systems. Classification I90 as I duct according to DIN 4102 Part 11 and classification E30 as E duct according to DIN 4102 Part 12.

Mounting of the duct directly on walls or under ceilings.

Including countersunk head screws and sealing strip.
Including countersunk head screws and sealing strip.



Fibreglass lightweight concrete

Master data

Item number	7215144
Type	BSKD09-K1021
Description 1	Fire protection duct I90/E30
Description 2	Direct mounting
Manufacturer	OBO
Dimension	1000x105x210
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Metre
Weight	2201 kg
Weight unit	kg/100 m


Technical data sheet

PYROLINE® Con D BSK I90/E30 fire protection duct

Item number: 7215144



Dimensions



Length	1,000 mm
Width	290 mm
Height	165 mm
Dimension B	290 mm
Dimension b	210 mm
Dimension h	105 mm
Dimension H	165 mm

Technical data

Number of flammable sides	3
Cover fastening	Screw
Fire resistance class E – function maintenance	30
Fire resistance class I – installation duct	90
With perforation	no
Usable cross-section	22050 mm ²
Partitions possible	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete