

Technical data sheet

Rising vertical bend for PYROLINE® Con S BSKH09-K0521
fire protection duct
Item number: 7215654



Rising vertical bend for PYROLINE® Con S fire protection duct, type BSKH09-K0521, consisting of fibreglass lightweight concrete which is resistant to water and frost for the creation of vertical changes of direction (45°) of the duct. Mounted connectors ensure quick mounting in situ, whilst loosely placed covers ensure quick inspection and reassignment.

Including connection screws and sealing strips.
Including connection screws and sealing strips.



Fibreglass lightweight concrete

Master data


Item number	7215654
Type	BSKH09-VS0521
Description 1	Vertical bend rising
Description 2	for BSKH09-K0521
Manufacturer	OBO
Dimension	50x210
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Piece
Weight	905 kg
Weight unit	kg/100 pc.

Technical data sheet

Rising vertical bend for PYROLINE® Con S BSKH09-K0521
fire protection duct
Item number: 7215654



Dimensions



External dimensions	338 x 140
Internal dimensions	210 x 50
Width	338 mm
Dimension B	338 mm
Dimension b	210 mm
Dimension h	50 mm
Dimension H	140 mm
Dimension L	204 mm

Technical data

Number of flammable sides	4
Cover fastening	Loose
Fire resistance class E – function maintenance	30
Fire resistance class I – installation duct	90
With perforation	no
Partitions possible	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete
Angle of the bend	45 °