

Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104241



Profile rail, perforated, slot width 17 mm, 150 x 35 x 18



- St** Steel
- FS** Strip galvanized

Master data		
Item number	1104241	
Type	CML3518P0150FS	
Description 1	Profile rail	
Description 2	perforated, slot 17mm	
Manufacturer	OBO	
Dimension	150x35x18	
Material	Steel	
Surface	Strip galvanized	
Surface standard	DIN EN 10346	
Smallest sales unit	25	
Unit of quantity	Piece	
Weight	10.6 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,2761 kg COe / 1 Piece	


Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104241



Dimensions



Length	150 mm
Width	35 mm
Height	18 mm
Dimension L	150 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Maintain electrical functions	yes
Material thickness	1.25 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value A	0.88 cm ²
Static value Iy	0.41 cm
Static value Iz	1.81 cm
Static value Wy	0.41 cm ²
Static value Wz	1.03 cm ²