

Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104325



Light-duty profile rail, perforated, slot width 17 mm.



- St** Steel
- FS** Strip galvanized

Master data	
Item number	1104325
Type	CML3518P0900FS
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	900x35x18
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	10
Unit of quantity	Piece
Weight	63.9 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,6049 kg COe / 1 Piece


Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104325



Dimensions



Length	900 mm
Width	35 mm
Height	18 mm
Dimension L	900 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Maintain electrical functions	yes
Material thickness	1.25 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value A	0.88 cm ²
Static value Iy	0.41 cm
Static value Iz	1.81 cm
Static value Wy	0.41 cm ²
Static value Wz	1.03 cm ²