

# Technical data sheet

## CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104497



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.



- St** Steel
- FS** Strip galvanized

Master data	
Item number	1104497
Type	CML3518P1000FS
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	1000x35x18
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Metre
Weight	71 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	1,7943 kg COe / 1 Meter


# Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104497



## Dimensions



Length	1,000 mm
Width	35 mm
Height	18 mm
Dimension L	1,000 mm

## Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Bundle	10 m
Maintain electrical functions	yes
Material thickness	1.25 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value A	0.88 cm <sup>2</sup>
Static value Iy	0.41 cm
Static value Iz	1.81 cm
Static value Wy	0.41 cm <sup>2</sup>
Static value Wz	1.03 cm <sup>2</sup>