

Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104500



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.



St	Steel
FS	Strip galvanized

Master data

Item number	1104500
Type	CML3518P2000FS
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	2000x35x18
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	71 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	1,7671 kg COe / 1 Meter


Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104500



Dimensions



Length	2,000 mm
Width	35 mm
Height	18 mm
Dimension L	2,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Bundle	20 m
Maintain electrical functions	yes
Material thickness	1.25 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value A	0.88 cm ²
Static value Iy	0.41 cm
Static value Iz	1.81 cm
Static value Wy	0.41 cm ²
Static value Wz	1.03 cm ²