


Technical data sheet

Cable tray EKS 60 FS

Item number: 6056628



EKS 60 = extra-heavy cable tray system with 60 mm side height.
Straight connectors should be ordered separately for all the versions.
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



- St** Steel
- FS** Strip galvanized

Master data		
Item number	6056628	
Description 1	Cable tray EKS	
Description 2	perforated	
Manufacturer	OBO	
Dimension	60x600x3000	
Colour	zinc	
Material	Steel	
Surface	Strip galvanized	
Surface standard	DIN EN 10346	
Smallest sales unit	3	
Unit of quantity	Metre	
Weight	997.333 kg	
Weight unit	kg/100 m	
CO Footprint (GWP) Cradle-to-Gate	52,6696 kg COe / 1 Meter	


Technical data sheet

Cable tray EKS 60 FS

Item number: 6056628



Dimensions



Dimension	60 x 600
Length	3,000 mm
Length	118 ft
Width	600 mm
Width	24 in
Height	60 mm
Height	2 in
Plate thickness	0.1 in
Plate thickness	2 mm
Dimension B	600 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Walkable	no
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	358 cm ²
Usable cross-section	35800 mm ²
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

Technical data sheet


Cable tray EKS 60 FS

Item number: 6056628



Loads

Insertable support spacings, min.	1.5 m
Insertable support spacings, max.	3 m
Support spacing 1.5 m	2.1 kN/m
Support spacing 2.0 m	1.35 kN/m
Support spacing 2.5 m	1.15 kN/m
Support spacing 3.0 m	0.9 kN/m



Load diagram, cable tray, type EKS 60

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width