

Technical data sheet

Service pole, type ISS130130

Item number: 6289405



Aluminium floor-ceiling service pole (surface anodised or powder-coated in RAL 9010) with two 76.5 system openings to accept device installation sockets of the 71GD series.

The service pole is fitted with an internal clamping device, which enables convenient tensioning between floor and ceiling. An extendable telescope provides a clamping range of 3,015–4,500 mm. Cables can be inserted both through the telescopic square pipe and directly into the main profile from below or above.

The installation area for switching and connection devices depends on the length of the extended telescope, but is at least 1 m per system opening (starting from the ground).

The service pole conforms to the requirements of DIN EN 50085.



Alu Aluminium

EL Anodised

Master data

Item number	6289405
Type	ISS130130EL
Description 1	service pole
Description 2	floor/ceiling
Manufacturer	OBO
Dimension	3000x130x130
Colour	aluminium
Material	Aluminium
Surface	Anodised
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	1600 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	142,7296 kg CO2e / 1 Piece


Technical data sheet

Service pole, type ISS130130

Item number: 6289405



Dimensions



Length	3,000 mm
Width	130 mm
Height	130 mm

Technical data sheet

Service pole, type ISS130130

Item number: 6289405



Technical data

Number of usable covers	2
Number of compartments	2 St.
Version for	Double-sided
Fastening type	Tension
Floor mounting	yes
Ceiling mounting	yes
Continuous profile	yes
Halogen-free	yes
Height compensation, max.	1500 mm
Height compensation, min.	15 mm
Cable entry	Top/bottom
Cover width	76.5 mm
Changes according to location	no
Pole shape	Square
Pole height, max.	4500 mm
Pole height, min.	3015 mm
Adjustable	yes
Pre-wired	no