


Technical data sheet

Mesh cable tray GR-Magic® 55 A4

Item number: 6001087



Mesh cable tray with shaped connector of side height 55 mm.
No additional connection components are required for the mesh cable tray, it is simply interlocked. The grid width is 50 x 100 mm (exception: GRM 55/50 = 20 x 100 mm).
Magnetic shield insulation without cover 15 dB, with cover 25 dB.



- A4Stainless steel
- 2BBright, treated

Master data	
Item number	6001087
Description 1	Mesh cable tray GRM
Manufacturer	OBO
Dimension	55x50x3000
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	3
Unit of quantity	Metre
Weight	67 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	3,4099 kg COe / 1 Meter


Technical data sheet

Mesh cable tray GR-Magic® 55 A4


Item number: 6001087



Dimensions



Length	3,000 mm
Width	50 mm
Width	1.97 in
Height	55 mm
Height	2.17 in
Dimension B	52 mm
Dimension H	58 mm



Technical data sheet


Mesh cable tray GR-Magic® 55 A4

Item number: 6001087



Technical data		
Connector version	Integrated connector	
Mounting system fastening type	Floor Ceiling Wall	
Maintain electrical functions	yes	
Integrated partition	Without	
Usable cross-section	16 cm²	
Usable cross-section	1600 mm²	
Profile shape	U-shaped	
Rustproof steel, pickled	yes	
Screwless connector	yes	
Wide-span version	no	
Load test type according to IEC 61537	Type II	
Type of connector, cable support system	Click fastening	

Loads		
Insertable support spacings, min.	1 m	
Insertable support spacings, max.	2.5 m	
Support spacing 1.0 m	0.35 kN/m	
Support spacing 1.5 m	0.2 kN/m	
Support spacing 2.0 m	0.1 kN/m	
Support spacing 2.5 m	0.1 kN/m	



Load diagram, mesh cable tray, type GRM 55 VA

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width