

# Technical data sheet

LG 60 cable ladder, 3 m VSF FT

Item number: 6207540



Cable ladder for horizontal routing of cables. Can be used in the widths 200–400 mm as a standard support structure for the maintenance of electrical functionality according to DIN 4102 Part 12. Maintenance of electrical functionality classes E30 to E90. With riveted C profile rung, open in an upward direction.



E30 E60 E90

St Steel

FT Hot-dip galvanised

## Master data

|                                   |                              |
|-----------------------------------|------------------------------|
| Item number                       | 6207540                      |
| Type                              | LG 620 VSF 3 FT              |
| Description 1                     | Cable ladder function maint. |
| Description 2                     | rungs distance 150 mm        |
| Manufacturer                      | OBO                          |
| Dimension                         | 60x200x3000                  |
| Colour                            | zinc                         |
| Material                          | Steel                        |
| Surface                           | Hot-dip galvanised           |
| Surface standard                  | DIN EN ISO 1461              |
| Smallest sales unit               | 3                            |
| Unit of quantity                  | Metre                        |
| Weight                            | 332.666 kg                   |
| Weight unit                       | kg/100 m                     |
| CO Footprint (GWP) Cradle-to-Gate | 7,489 kg COe / 1 Meter       |


# Technical data sheet

LG 60 cable ladder, 3 m VSF FT

Item number: 6207540



## Dimensions



|                     |          |
|---------------------|----------|
| Length              | 3,000 mm |
| Width               | 200 mm   |
| Height              | 60 mm    |
| Dimension B         | 200 mm   |
| Rung slot dimension | 17.00    |

## Technical data

|                               |                      |
|-------------------------------|----------------------|
| Version of the rungs          | Profile perforated   |
| Side rail version             | Profile (open)       |
| Fastening of rung             | Blind riveted        |
| Maintain electrical functions | yes                  |
| Usable cross-section          | 9800 mm <sup>2</sup> |
| Rustproof steel, pickled      | no                   |
| Side perforation              | yes                  |
| Rung distance                 | 150 mm               |
| Wide-span version             | no                   |
| Rail thickness                | 1.5 mm               |