

Technical data sheet

LightningController - MCF75-NAR-TNC+FS

Item number: 5096983



- Combination arrester, type 1+2, for mounting on 40 mm busbars, for TN-C systems
- Protection level ≤ 1.5 kV to protect the terminals
 - Lightning protection equipotential bonding according to VDE 0185-305 (IEC 62305)
 - Lightning current arresting capacity up to 75 kA (10/350) 3-pole
 - Fulfils the requirements of VDE 0100-534 (IEC 60364-5-53)
 - Line follow current quenching up to 50 kA and max. backup fuse up to 315 A gL/gG
 - Spark gaps for use in the pre-meter area according to VDE-AR-N 4100
 - With potential-free changeover contact for remote signalling
- Application: Buildings with lightning protection or outside cable infeed.



Master data		
Item number	5096983	
Type	MCF75-NAR-TNC+FS	
Description 1	LightningController Rail	
Description 2	3-pole with RS	
Manufacturer	OBO	
Dimension	255V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	102 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	5,3831 kg CO2e / 1 Piece	


Technical data sheet

LightningController - MCF75-NAR-TNC+FS

Item number: 5096983




Dimensions



Length	226 mm
Width	50 mm
Height	109 mm

Technical data



Arrester surge current (8/20 µs) [total]	75 kA
Connection cross-section (min.)	10 mm²
Connection cross-section, FM terminals, max.	16 AWG
Connection cross-section, FM terminals, max.	1.5 mm²
Connection cross-section, FM terminals, min.	28 AWG
Connection cross-section, FM terminals, min.	0.5 mm²
Response time	<100 ns
Response time [L-N]	<100 ns
Response time [N-PE]	<100 ns
Version for	3+NPE
Pole version	3
Structural width in division units (division unit, 17.5 mm)	Miscellaneous
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	25 kA
Lightning surge current (10/350)	75 kA
Torque	35 Lbs
Torque	3.5 Nm
Torque for FM terminal	1.7 Lbs
Torque for FM terminal	0.2 Nm
Installation location	Interior
Remote signalling	yes
FM contacts	Changeover
Function/defect display	Visual
Housing material surge protection components	PA UL 94 V-0
Combined voltage protection level [L-PEN]	1.5 kV
Maximum continuous voltage (L-N)	255 V


Technical data sheet

LightningController - MCF75-NAR-TNC+FS

Item number: 5096983



Technical data



Maximum continuous voltage AC	255 V
Short-circuit resistance for max. mains-side overcurrent protection	50 kA eff
Conductor cross-section, flexible (fine-wire), max.	35 mm ²
Conductor cross-section, flexible (fine-wire), max.	2 AWG
Conductor cross-section, flexible (fine-wire), min.	7 AWG
Conductor cross-section, flexible (fine-wire), min.	10 mm ²
Conductor cross-section, rigid (single-wire/multiwire), max.	2 AWG
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	7 AWG
Conductor cross-section, rigid (single-wire/multiwire), min.	10 mm ²
Humidity, max.	95 %
Humidity, min.	5 %
Max. mains-side overcurrent protection	315 A
Maximum back-up fuse	315 A
Maximum discharge current (8/20 µs)	50 kA
Maximum discharge current (8/20 µs) [L-N]	50 kA
Minimum distance	0 mm
Installation type	Bus bar 40 mm
Nominal discharge current (8/20 µs)	25 kA
Nominal discharge current (8/20 µs) [L-N]	25 kA
Nominal frequency	50 Hz
Nominal voltage AC (50/60 Hz)	230 V
Network form	TN-C
TN network form	yes
TN-C network form	yes
Ports	One-Port SPD
Switching power AC	250 V/ 2 A
Switching power DC	250 V/ 0,1 A
Protection rating	IP20
Protection level	≤1,5
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2
SPD to IEC 61643-1	Class I+II
TOV voltage [L-N] – fail safe mode – 120 min.	442 V
TOV voltage [L-N] – withstand mode – 5 s	440 V
Approvals	VDE
Cable type for surge protection devices	Power cable AV