

Technical data sheet

LG 60 cable ladder, 6 m VSF

Item number: 6207509



Cable ladder for the horizontal routing of cables. Can be used as a standard support structure for the maintenance of electrical functionality according to DIN 4102 Part 12. Maintenance of electrical function classes E30 to E90. With riveted C profile rung, open in an upward direction.

E30 E60 E90

St Steel

FS Strip galvanized

Master data		
Item number	6207509	
Description 1	Cable ladder function maint.	
Description 2	rungs distance 150 mm	
Manufacturer	OBO	
Dimension	60x400x6000	
Colour	zinc	
Material	Steel	
Surface	Strip galvanized	
Surface standard	DIN EN 10346	
Smallest sales unit	6	
Unit of quantity	Metre	
Weight	407.166 kg	
Weight unit	kg/100 m	
CO Footprint (GWP) Cradle-to-Gate	10,15 kg COe / 1 Meter	


Technical data sheet

LG 60 cable ladder, 6 m VSF



Item number: 6207509

Dimensions



Length	6,000 mm
Width	400 mm
Height	60 mm
Dimension B	400 mm
Rung slot dimension	17.00

Technical data

Version of the rungs	Profile perforated
Side rail version	Profile (open)
Fastening of rung	Blind riveted
Maintain electrical functions	yes
Usable cross-section	198 cm ²
Usable cross-section	19800 mm ²
Rustproof steel, pickled	no
Side perforation	yes
Rung distance	150 mm
Wide-span version	no
Rail thickness	1.5 mm