

Technical data sheet

Series protection device, 3-pole, 5 V version

Item number: 5098407



Lightning barrier with test function; 5 V version

- Nominal load current 0.58 A
- Protection device for multi-wire systems
- Direct shield earthing and screwless connection terminals
- Space-saving width of just 8.7 mm
- Protection circuit testable with Life Control
- High frequency range of 0–100 MHz
- UL-listed (4DG1)

Application: Universal use on 35 mm DIN profile rail in any standard distribution housing.



Master data

Item number	5098407
Description 1	Lightning barrier
Description 2	3-pole with test function
Manufacturer	OBO
Dimension	5V
Smallest sales unit	1
Unit of quantity	Piece
Weight	6 kg
Weight unit	kg/100 pc.


Technical data sheet

Series protection device, 3-pole, 5 V version


Item number: 5098407



Dimensions



Technical data



Arrestor monitoring	no
Connection cross-section, flexible, max.	2.5 mm ²
Connection cross-section, flexible, min.	0.14 mm ²
Connection cross-section, multi-wire, max.	1.5 mm ²
Connection cross-section, multi-wire, min.	0.14 mm ²
Connection cross-section, rigid, max.	2.5 mm ²
Connection cross-section, rigid, min.	0.14 mm ²
Number of poles	3
Insertion loss	≤3 dB
Earthing via:	DIN rail
Explosion-tested version	no
Telecommunications contact	no
Total discharge current (10/350)	D1: 1,5 kA
Total discharge current (8/20)	7.5 kA
Cut-off frequency	100 MHz
Maximum continuous voltage AC	7 V
Maximum continuous voltage DC	10 V
Insulation resistance	>10 MΩ
Capacity (wire-wire)	< 40 pF
Kategorie	Type 1+2+3 / D1+C2+C1
Lightning protection zone LPZ	0→3
Mounting type	DIN rail 35 mm
Nominal load current AC	0.4 A
Nominal load current DC	0.58 A
Nominal voltage	5 V
Testing standard	IEC 61643-21
Shielding connection available	yes
Screening	Direct
Protection rating	IP20
Protection level @ C1	<50 V
Protection level wire-wire	<35 V
Protection level wire-earth	<800 V

Technical data sheet

Series protection device, 3-pole, 5 V version

Item number: 5098407



Technical data		
	Series resistance per wire	2,35 Ω ± 5 %
	Signalling on device	Readable
	SPD to IEC 61643-21	Class I+II+III / D1+C2+C1
	Plug-in system	Terminal
	Impulse durability wire-wire	C1: 0,5 kV / 0,25 kA (8/20µs)
	Impulse durability wire-earth	C2: 5 kV / 2,5 kA (8/20µs)
	Permitted temperature range, max.	80 °C
	Permitted temperature range, min.	-40 °C
	Approvals	UL