


# Technical data sheet

## Cable tray, marine standard FS

Item number: 6046375



Cable tray for use in ship construction, produced according to the marine standard VG 88900-1.



**St** Steel

**FS** Strip galvanized

### Master data

|                                   |                            |
|-----------------------------------|----------------------------|
| Item number                       | 6046375                    |
| Description 1                     | Cable tray marine standard |
| Description 2                     | Material thickness 1.25mm  |
| Manufacturer                      | OBO                        |
| Dimension                         | 15x125x2000                |
| Colour                            | zinc                       |
| Material                          | Steel                      |
| Surface                           | Strip galvanized           |
| Surface standard                  | DIN EN 10346               |
| Smallest sales unit               | 2                          |
| Unit of quantity                  | Metre                      |
| Weight                            | 113.4 kg                   |
| Weight unit                       | kg/100 m                   |
| CO Footprint (GWP) Cradle-to-Gate | 4,9519 kg COe / 1 Meter    |


# Technical data sheet

## Cable tray, marine standard FS

Item number: 6046375



### Dimensions



|                 |          |
|-----------------|----------|
| Length          | 2,000 mm |
| Width           | 125 mm   |
| Height          | 15 mm    |
| Plate thickness | 1.25 mm  |
| Dimension B     | 125 mm   |

### Technical data

|                                         |                    |
|-----------------------------------------|--------------------|
| Connector version                       | Without connectors |
| Walkable                                | no                 |
| Maintain electrical functions           | no                 |
| With cover                              | no                 |
| Mounting perforation in base            | yes                |
| NATO hole pattern                       | yes                |
| Rustproof steel, pickled                | no                 |
| Side perforation                        | no                 |
| Wide-span version                       | no                 |
| Load test type according to IEC 61537   | Type II            |
| Type of connector, cable support system | Screwed            |

### Loads

|                       |          |
|-----------------------|----------|
| Support spacing 1.0 m | 0.6 kN/m |
| Support spacing 1.5 m | 0.2 kN/m |