

# Technical data sheet

## T piece 110 FS

Item number: 6219390



T piece to create a horizontal branch, fittings for cable ladders of side height 110 mm. With connector perforation. Can be used in indoor areas. Connector and fastening material must be ordered separately. Fittings must be supported by the support structure.



|    |                  |
|----|------------------|
| St | Steel            |
| FS | Strip galvanized |

### Master data

|                     |                              |
|---------------------|------------------------------|
| Item number         | 6219390                      |
| Type                | LT 1160 R5 FS                |
| Description 1       | T piece                      |
| Description 2       | for cable ladder, horizontal |
| Manufacturer        | OBO                          |
| Dimension           | 110x600                      |
| Colour              | zinc                         |
| Material            | Steel                        |
| Surface             | Strip galvanized             |
| Surface standard    | DIN EN 10346                 |
| Smallest sales unit | 1                            |
| Unit of quantity    | Piece                        |
| Weight              | 1155 kg                      |
| Weight unit         | kg/100 pc.                   |


# Technical data sheet

## T piece 110 FS

Item number: 6219390



### Dimensions



|             |        |
|-------------|--------|
| Width       | 600 mm |
| Height      | 110 mm |
| Dimension B | 600 mm |
| Dimension R | 500 mm |

### Technical data

|                               |                      |
|-------------------------------|----------------------|
| Version of the rungs          | Profile unperforated |
| Side rail version             | Flat profile         |
| Type                          | Exit symmetrical     |
| Maintain electrical functions | no                   |
| Rustproof steel, pickled      | no                   |
| Wide-span version             | no                   |
| Rail thickness                | 1.5 mm               |