

Technical data sheet

Coordinated LightningController MCD 50-B-OS-320



Item number: 5096861



- Lightning arrester, type 1
- Voltage protection level < 1.3 kV, allows device protection
 - For lightning protection equipotential bonding to VDE 0185-305 (IEC 62305)
 - Lightning current arresting capacity to 50 kA (10/350) per pole and up to 150 kA (10/350) in total
 - Line following current quenching 25 kA Ipeak, arrester backup fuse to 500 A gL/gG
 - Encapsulated, non-extinguishing spark gap arrester for use in distributor housings
- Application: Industrial systems and buildings with external lightning protection of the classes I to IV.



Master data		
Item number	5096861	
Type	MCD 50-B-OS-320	
Description 1	CoordinatedLightningController	
Description 2	with function display	
Manufacturer	OBO	
Dimension	320V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	34.8 kg	
Weight unit	kg/100 pc.	

Dimensions		
	Length	100 mm
	Width	35 mm
	Height	69 mm

Technical data sheet

Coordinated LightningController MCD 50-B-OS-320

Item number: 5096861



Technical data



Arrester surge current (8/20 µs) [total]	50 kA
Response time	<100 ns
Blow-out	no
Pole version	1
Structural width in division units (division unit, 17.5 mm)	2
Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	50 kA
Lightning surge current (10/350)	50 kA
Remote signalling	no
Follow current quenching capacity (eff) [N-PE]	10 kA
Follow current quenching capacity leff	7
Maximum continuous voltage AC	320 V
Short-circuit resistance	25 kA
Short-circuit resistance for max. mains-side overcurrent protection	25 kA
Conductor cross-section, rigid (single-wire/multiwire), max.	50 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	10 mm ²
Lightning protection zone LPZ	0→2
Max. mains-side overcurrent protection	500
Maximum back-up fuse	500 A
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	50 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	TN-C
Test class, type 1	yes
Protection rating	IP20
Protection level	1,3
Signalling on device	Visual
SPD to EN 61643-11	Type 1
SPD to IEC 61643-1	Class I