


Technical data sheet

MMS-plus P 6x40 round head tie, with pan head

Item number: 3498105



Bolt tie for direct mounting without additional anchors in cracked and uncracked concrete and masonry. With round head for universal fastenings. Torx drive T30.

Construction product tested according to EAD and CE mark, with European Technical Assessment (ETA) and proof of suitability. Load-bearing capacities under fire loads proven up to fire resistance class R120.
Substrate

The screw ties are suitable for screwing into the following types of masonry:

- Calcareous sandstone - Full brick (KSV)
- Calcareous sandstone - Hollow brick (KSL)
- Whole brick (Vz)



St Steel

G Electrogalvanized

Master data

Item number	3498105
Type	MMS+ P 6x40
Description 1	Screw anchor
Description 2	with panhead
Manufacturer	OBO
Dimension	6x40mm
Colour	zinc
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	100
Unit of quantity	Piece
Weight	1 kg
Weight unit	kg/100 pc.


Technical data sheet

MMS-plus P 6x40 round head tie, with pan head

Item number: 3498105



Dimensions



Dimension	6 x 40
Length	40 mm
Dimension L	40 mm

Technical data

Anchor/nail/bolt version	Spiral anchor
Drill hole diameter, min.	5 mm
Thread diameter ST	6
Head diameter	11.2 mm
Head shape	Miscellaneous
Screw system	Torx