

Technical data sheet

MS4022 mounting rail, heavy duty, slot 18 mm, FT, perforated

Item number: 1121898



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	1121898
Type	MS4022P6000FT
Description 1	Profile rail
Description 2	perforated, slot 18mm
Manufacturer	OBO
Dimension	6000x40x22,5
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	6
Unit of quantity	Metre
Weight	152.5 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to- Gate	3,3077 kg COe / 1 Meter


Technical data sheet

MS4022 mounting rail, heavy duty, slot 18 mm, FT, perforated

Item number: 1121898



Dimensions



Length	6,000 mm
Width	40 mm
Height	22.5 mm
Dimension L	6,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	no
Material thickness	2 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	18 mm
Static value A	1.74 cm ²
Static value I _y	1.18 cm
Static value I _z	4.45 cm
Static value W _y	1.05 cm ²
Static value W _z	2.23 cm ²