

Technical data sheet



MMS-plus P 7.5x80 round head bolt tie, with pan head

Item number: 3498272



Bolt tie for direct mounting without additional anchors in cracked and uncracked concrete and masonry. With round head for universal fastenings. Torx drive T30.

Construction product tested according to EAD and CE mark, with European Technical Assessment (ETA) and proof of suitability. Load-bearing capacities under fire loads proven up to fire resistance class R120.



| | |
|-----------|-------------------|
| St | Steel |
| G | Electrogalvanized |

Master data

| | |
|---------------------|----------------------------|
| Item number | 3498272 |
| Type | MMS+ P 7.5x80 |
| Description 1 | Screw anchor |
| Description 2 | with panhead |
| Manufacturer | OBO |
| Dimension | 7,5x80mm |
| Colour | zinc |
| Material | Steel |
| Surface | Electrogalvanized |
| Surface standard | EN ISO 19598 / EN ISO 4042 |
| Smallest sales unit | 50 |
| Unit of quantity | Piece |
| Weight | 1.6 kg |
| Weight unit | kg/100 pc. |


Technical data sheet

MMS-plus P 7.5x80 round head bolt tie, with pan head

Item number: 3498272



Dimensions



| | |
|-------------|----------|
| Dimension | 7,5 x 80 |
| Length | 80 mm |
| Dimension L | 80 mm |



T30

Technical data

| | |
|---------------------------|---------------|
| Drill hole diameter, min. | 6 mm |
| Thread diameter ST | 7.5 |
| Head diameter | 14.5 mm |
| Head shape | Miscellaneous |
| Screw system | Torx |