

# Technical data sheet

## Wall and support bracket MWAG 12 A2

Item number: 6424406



Light-duty wall and support bracket with edged design for screwless mesh cable tray fastening.  
Including truss-head bolt M10 x 25 for fastening to U supports.  
Including truss-head bolt M10 x 25 for fastening to U supports.



|    |                 |
|----|-----------------|
| A2 | Stainless steel |
| 2B | Bright, treated |

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 6424406                  |
| Type                               | MWAG 12 41 A2            |
| Description 1                      | Wall and support bracket |
| Description 2                      | for mesh cable tray      |
| Manufacturer                       | OBO                      |
| Dimension                          | B410mm                   |
| Colour                             | stainless steel          |
| Material                           | Stainless steel          |
| Surface                            | Bright, treated          |
| Surface standard                   |                          |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 69.2 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 4,4158 kg CO2e / 1 Piece |


# Technical data sheet

## Wall and support bracket MWAG 12 A2

Item number: 6424406



### Dimensions



|             |        |
|-------------|--------|
| Width       | 410 mm |
| Height      | 83 mm  |
| Dimension A | 38 mm  |
| Dimension B | 410 mm |
| Dimension H | 83 mm  |

### Technical data

|                               |                          |
|-------------------------------|--------------------------|
| Version for                   | Wall and support bracket |
| F in kN                       | 1.2 kN                   |
| Maintain electrical functions | no                       |
| for width min.                | 400                      |
| Hole diameter                 | 11 mm                    |
| Rustproof steel, pickled      | no                       |
| Angle range, max.             | 90 mm                    |
| Angle range, min.             | 90 mm                    |


### Characteristic anchor load values for wall and support bracket MWAG 12

#### Wall fastening

|                | Max. load [kN]     |     |     |     |
|----------------|--------------------|-----|-----|-----|
|                | Bracket width [mm] |     |     |     |
| Anchor type    | 110                | 210 | 310 | 410 |
| BZ3 10x90/0-30 | 1.2                | 1.2 | 1.2 | 1.2 |

Max. Belastung F ges. = Kabelgewicht + Kabelrinne + Ausleger. Die angegebenen Werte basieren auf gerissenem Beton der Festigkeitsklasse C20/25. Die Einbaubedingungen der ETA-Zulassung (Dübel) sind zu beachten!

### Load values for MWAG 12 on suspended support



|                  | Max. total load F in kN |     |     |     |
|------------------|-------------------------|-----|-----|-----|
|                  | Bracket length in mm    |     |     |     |
| Support          | 100                     | 200 | 300 | 400 |
| US 3 K/ 20 - 60  | 1.2                     | 1.2 | 1.2 | 1.2 |
| US 3 K/ 70 - 120 | 1.2                     | 1.2 | 1.2 | 1.2 |
| US 5 K/ 20 - 60  | 1.2                     | 1.2 | 1.2 | 1.2 |
| US 5 K/ 70 - 120 | 1.2                     | 1.2 | 1.2 | 1.2 |