

Technical data sheet

Plug-in arrester PDP, 2x2-pole

Item number: 5080414



Plug-in arrester, plug-in data protection type 1+2/D1+C2 for use in instrumentation, control and automation equipment

- Protection device for multiwire systems
- Frequency range to 100 MHz
- Small width of 12.5 mm

Application: Universal lightning and surge protection for data transmission devices in MCR technology.



Master data		
Item number	5080414	
Type	PDP-P-2x2-24	
Description 1	Pluggable data line protection	
Description 2	plug-in arrester 2x2-pole	
Manufacturer	OBO	
Dimension	24V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	2.4 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to- Gate	0,2129 kg CO2e / 1 Piece	


Technical data sheet

Plug-in arrester PDP, 2x2-pole

Item number: 5080414




Dimensions



Length	51 mm
Width	13 mm
Height	46 mm

Technical data



Connection cross-section, flexible, max.	1.5 mm ²
Connection cross-section, flexible, min.	0.14 mm ²
Connection cross-section, multi-wire, max.	2.5 mm ²
Connection cross-section, multi-wire, min.	0.14 mm ²
Connection cross-section, rigid, max.	2.5 mm ²
Connection cross-section, rigid, min.	0.14 mm ²
Insertion loss	≤3 dB
Earthing via:	Connection cable / DIN rail
Total discharge current (10/350)	2.5 kA
Total discharge current (8/20)	20 kA
Cut-off frequency	100 MHz
Maximum continuous voltage AC	21 V
Maximum continuous voltage DC	30 V
Lightning impulse current	2.5 kA
Capacity (wire-wire)	≤30 pF
Capacity (wire-earth)	≤30 pF
Kategorie	Type 1+2 / D1+C2
Lightning protection zone LPZ	0→2
Lengthwise resistance	1.2 ± 5%
Mounting of input / output	Screw terminals
Mounting type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	10 kA
Nominal load current AC	0.425 A
Nominal load current DC	0.6 A
Total impulse durability into C2 (8/20)	20 kA
Testing standard	IEC 61643-21
Shielding connection available	yes
Screening	Direct
Protection rating	IP20
Protection level wire-wire	150 V
Series resistance per wire	1.2 Ω ± 5%
Signalling on device	None
SPD to EN 61643-11	Type 1+2
SPD to IEC 61643-1	Class I+II

Technical data sheet

Plug-in arrester PDP, 2x2-pole

Item number: 5080414



Technical data



SPD to IEC 61643-21

Class I+II / D1+C2

Plug-in system

Terminal

Impulse durability wire-wire

10 kV / 5 kA

Impulse durability wire-earth

10 kV / 5 kA

Permitted temperature range,
max.

80 °C

Permitted temperature range,
min.

-40 °C

