

Technical data sheet

Protection set MCD + V20 3-pole

Item number: 5089754



- Protection set, lightning and surge arrester combination, type 1+2
- For lightning protection equipotential bonding to VDE 0185-305 (IEC 62305)
 - Lightning current arresting capacity to 50 kA (10/350) per pole
 - Arrester, connectable, incl. connecting bridges, labelled connection terminals
 - Encapsulated, non-extinguishing arrester for use in distributor housings
- Application: Mobile telecommunications systems and industrial systems with special requirements.



Master data	
Item number	5089754
Description 1	Protection set
Description 2	3-pole version
Manufacturer	OBO
Dimension	255V
Smallest sales unit	1
Unit of quantity	Piece
Weight	158 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	3,4792 kg COe / 1 Piece


Technical data sheet

Protection set MCD + V20 3-pole

Item number: 5089754



Dimensions



Technical data

Arrester surge current (8/20 µs) [total]	100 kA
Response time	<25 ns
Blow-out	no
Version for	3-pole; 255 V
Pole version	3
Structural width in division units (division unit, 17.5 mm)	10th
Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	50 kA
Lightning surge current (10/350)	100 kA
Remote signalling	no
Follow current quenching capacity (eff) [N-PE]	25 kA
Follow current quenching capacity I _{eff}	12.5
Maximum continuous voltage (L-N)	255 V
Maximum continuous voltage AC	255 V
Short-circuit resistance	25 kA
Short-circuit resistance for max. mains-side overcurrent protection	25 kA
Conductor cross-section, rigid (single-wire/multiwire), max.	50 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	10 mm ²
Lightning protection zone LPZ	0→2
Max. mains-side overcurrent protection	125
Maximum back-up fuse	125 A
Maximum discharge current (8/20 µs)	100 kA
Nominal discharge current (8/20 µs)	50 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	TN-C
Pole number	3
Protection rating	IP20
Protection level	≤1,7
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2

Technical data sheet

Protection set MCD + V20 3-pole

Item number: 5089754



Technical data

SPD to IEC 61643-1

Class I+II

