

Technical data sheet

Installation duct with PYROLINE® Rapid PLM fire protection mesh, duct height 80 mm, FS
Item number: 7218008



Metal installation duct with intumescent fire protection mesh for fireproof routing of cables. Classified as an installation duct EI30, EI60 and EI90 according to EN 13501-2, tested according to EN 1366-5. The duct prevents the fire spread for the classified period of time, offering protection against the effects of a cable fire.

Suitable for direct wall and ceiling mounting, mounting below system floors and on support systems. Tool-free joint mounting with PLM SI joint connector. Only approved pre-terminated fittings may be used. The cover is snapped on without tools, allowing rapid inspection and retroassignment. Offset cover mounting for continuous equipotential bonding of the entire duct section.



St	Steel
FS	Strip galvanized

Master data

Item number	7218008
Description 1	Installation duct metal
Description 2	with fire protection mesh
Manufacturer	OBO
Dimension	80x100x2000
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	379.5 kg
Weight unit	kg/100 m

Dimensions

Length	2,000 mm
Width	100 mm
Height	80 mm
Dimension B	100 mm
Dimension H	80 mm
Dimension i	62 mm

Technical data sheet

Installation duct with PYROLINE® Rapid PLM fire protection mesh, duct height 80 mm, FS

Item number: 7218008



Technical data

Number of flammable sides	4
Cover fastening	Miscellaneous
Classification EI – installation duct	90
With perforation	yes
Usable cross-section	5180 mm ²
Partitions possible	yes
Jacketing	Steel
Internal height	74 mm
Internal width	94 mm
maximum specific impedance Z ₁	2 mΩ/m