


Technical data sheet

Bend, angle-adjustable, 60 FS

Item number: 6037110



Angle-adjustable bend for the creation of a horizontal branch, fitting for lock and screw-on cable trays of side height 60 mm. Adjustable angle 0–90°. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used in indoor areas. Fastening material must be ordered separately.



St

Steel

FS

Strip galvanized

Master data

Item number	6037110
Type	RB W 650 FS
Description 1	Adjustable bend
Description 2	horizontal
Manufacturer	OBO
Dimension	60x500
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	308.2 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	13,021 kg CO2e / 1 Piece


Technical data sheet

Bend, angle-adjustable, 60 FS

Item number: 6037110



Dimensions



Width	500 mm
Height	60 mm
Plate thickness	1.25 mm
Dimension B	500 mm
Dimension L	992 mm
Dimension R	50 mm

Technical data

Bend (angle)	Adjustable
Connector version	Integrated connector
Type	Adjustable bend_complete
Maintain electrical functions	no
Material thickness, floor plate	1.25 mm
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Change of direction	Horizontal
Rustproof steel, pickled	no
Side perforation	yes
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	screwed/clamped
Recommended quantity of bolts	16 St.
Rail thickness	1.25 mm