

Technical data sheet

90° vertical bend, falling 60 A4

Item number: 7006770



90° vertical bend, falling, for all cable tray types of 60 mm side height.
The vertical bend is pushed over the end of the cable tray and screwed tight.
Fastening materials should be ordered separately.



A4 Stainless steel

2B Bright, treated

Master data

| | |
|---------------------|-------------------|
| Item number | 7006770 |
| Description 1 | 90° vertical bend |
| Description 2 | falling |
| Manufacturer | OBO |
| Dimension | 60x600 |
| Colour | stainless steel |
| Material | Stainless steel |
| Surface | Bright, treated |
| Surface standard | |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 176 kg |
| Weight unit | kg/100 pc. |


Technical data sheet

90° vertical bend, falling 60 A4

Item number: 7006770



Dimensions



| | |
|-----------------|--------|
| Width | 600 mm |
| Width | 24 in |
| Height | 60 mm |
| Height | 2 in |
| Plate thickness | 1 mm |
| Dimension B | 600 mm |

Technical data

| | |
|---|--------------------|
| Bend (angle) | 90° |
| Connector version | Without connectors |
| Maintain electrical functions | no |
| Mounting perforation in base | no |
| NATO hole pattern | no |
| Change of direction | Vertical, falling |
| Rustproof steel, pickled | no |
| Side perforation | no |
| Wide-span version | no |
| Type of connector, cable support system | Screwed |